

NICOMATIC SA (HEADQUARTERS) 173, rue des Fougères - ZI Les Bracots F-74890 Bons-en-Chablais Téléphone: +33 4 50 36 13 85 – Fax: +33 4 50 36 11 33 Email: nicomatic@nicomatic.fr



16068-MO MANUAL PRESS 1.27mm pitch



NICOMATIC is certified ISO9001:2008 / EN9100:2003

NICOMATIC is now enriching the **CRIMPFLEX®** connector range to provide even **more space and cost-savings solutions** thanks to the **1,27 mm pitch**. Our specifically designed **Crimping Press** allows you to crimp up to 50 contacts in a single operation in order **to increase your productivity** and **eliminate any risk of pitch drift** during the crimping process.



Ni**gomati**g

0



16068-MO MANUAL PRESS 1.27mm pitch



How to crimp in only 5 steps?

1. Install 2 reels on the support, and select the number of contacts to be crimped





2. Unroll the cable and retrieve the paper protection

3. Position the 2 strips of contacts on top of each other (1st reel in front of you on top of the rear one)





4. Place the 2 parallel strips onto the pins and stop the reel of contacts with the 1st bolt action on the right side. Then crimp as indicated on 5^{th} step until the stop

part of this data sheet without prior notice - ©

nange the spec

nue the production

- 5. Test crimping with the positioning system
- Place the cable to the right side until stop
- Use the needle and LED light
- Lock the contacts by using the lever
- Crimp

www.nicomatic.com

Available on www.youtube.com